


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5"-0")								



SPECS: OVERMOLD: GRAY PVC INSERT: BLACK PVC COUPLING NUT: ANODIZED ALUMINUM CABLE: #10AWG GRAY PVC DUAL RATED UL TC/OPEN WIRING & ST00W ELECTRICAL: 600V AC/DC	ADDED PART NUMBER EC NO: IPG2016-1155 C			DRWNGGUSTAFSON 2016/02/23 CHKD:MZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23		QUALITY SYMBOLS ▽=0 ▽=0 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:2		DESIGN UNITS INCH		THIRD ANGLE PROJECTION		
	REV		DESCRIPTION		mm		INCH		DRAWN BY B. RUPERT		DATE 01/12/10		QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES				
	3 PLACES		± ---		± ---		±.005		CHECKED BY		DATE						
	2 PLACES		± ---		±.010		±.010		B. WOODMAN		DATE 01/12/10						
	1 PLACE		± ---		±.020		±.020		APPROVED BY		DATE 2010/01/15		MOLEX INCORPORATED				
					ANGULAR ±1/2°		ANGULAR ±1/2°		JFMURPHY								
									MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
									SEE CHART		SD-130064-065		1 OF 1				
									SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640170