


13	12	11	10	9	8	7	6	5	4	3	2	1
POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH								
3	1300640065	CC3030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640187	CC4030A48M020	32	2M +89-0MM (6'7"+3.50-0)								
4	1300640245	CC4030A48M100	32	10M +318-0MM (32'10" +12.5"-0")								



SPECs: OVERMOLD: GRAY PVC INSERT: BLACK PVC COUPLING NUT: ANODIZED ALUMINUM CABLE: #10AWG GRAY PVC DUAL RATED UL TC/OPEN WIRING & ST00W ELECTRICAL: 600V AC/DC	ADDED PART NUMBER EC NO: IPG2016-1155 C DRWNGGUSTAFSON 2016/02/23 CHKD:MZIELINSKI 2016/03/15 APPR:BMWOODMAN 2016/02/23				QUALITY SYMBOLS ▽=0 ▽=0 REV	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:2		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
	mm		INCH				DRAWN BY B. RUPERT		DATE 01/12/10		QUICK CHANGE FEMALE/MALE STRAIGHT 3 & 4 POLE AS PORTABLES MOLEX INCORPORATED					
	4 PLACES ± ---		± ---				CHECKED BY		DATE							
	3 PLACES ± ---		±.005				B. WOODMAN		01/12/10							
	2 PLACES ± ---		±.010				APPROVED BY		DATE							
	1 PLACE ± ---		±.020				JFMURPHY		2010/01/15		SD-130064-065					
	ANGULAR ±1/2°						MATERIAL NO.		DOCUMENT NO.						SHEET NO.	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		1 OF 1					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300640171