





ENG No: CC3130A64MXXX

LENGTH
M005 = 0.5M
M010 = 1M
M100 = 10M



SPECIFICATIONS:

OVERMOLD: BLACK PVC
INSERT: BLACK PVC
CONTACTS: COPPER ALLOY, GOLD OVER NICKEL
COUPLING NUT: ANODIZED ALUMINUM
CABLE (A64): #10/3 BLACK PVC
ELECTRICAL: 600V AC/DC, 30A
TEMPERATURE RATING: -20°C to 105°C
PROTECTION: IP67

RELEASED EC NO: IPG2015-2148 DRWN: GSUDHINI 2015/06/18 CHKD: BARDEN 2015/06/24 APPR: JFMURPHY 2015/08/27	DESCRIPTION REV	QUALITY SYMBOL <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY DATE	TITLE <div>QUICK CHANGE FEM/MALE STR/STR #10 BLK PVC</div> <div>MOLEX INCORPORATED</div>						
			4 PLACES	±---	±---	GSUDHINI 2015/06/18							
			3 PLACES	±---	±.005	CHECKED BY DATE							
			2 PLACES	±0.13	±.010	BARDEN 2015/06/24							
			1 PLACE	±0.25	±.020	APPROVED BY DATE							
			ANGULAR ±.5°			JFMURPHY 2015/08/27	 MOLEX INCORPORATED	DOCUMENT NO. SD-130064-007				SHEET NO. 1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE MATRIX							
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300642034