

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300920043](#)
Status: **Active**
Overview: [Slip Rings](#)
Description: Aero-Motive Enclosed Slip Ring, 30A, 10 AWG, 12 Conductors

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19099
UL	E110371

General

Product Family	Slip Rings
Series	130092
Center Bore Diameter	N/A
Component Type	Enclosed
Current - Maximum per Contact	30.0A
Mounting Style	Vertical
Number of Conductors	12
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 10
Temperature Range - Operating	-40°C to +120°C
UPC	78678867699
Voltage - Maximum	600V
Wire Size AWG	10

Material Info

Engineering Number	ISRC312
--------------------	---------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130092](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300920043](#)