

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300920168](#)
Status: **Active**
Overview: [Slip Rings](#)
Description: Aero-Motive Self-Contained Slip Ring, 17A, 14 AWG, 30 Conductors, Bore Size 38.10mm (1.500") Diameter

Documents:


[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Slip Rings
Series	130092
Center Bore Diameter	38.10mm (1.500")
Component Type	Self-Contained
Current - Maximum per Contact	17.0A
Mounting Style	Horizontal
Number of Conductors	30
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 125
Temperature Range - Operating	-40°C to +120°C
UPC	78678867811
Voltage - Maximum	600V
Wire Size AWG	14

Material Info

Engineering Number SR330



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130092](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300920168](#)