

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950123](#)

**Status:** **Active**

**Overview:** [Pulling Grips](#)

**Description:** Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Short Mesh Length 0.279m (11.00"), Approximate Break Strength 3084.43kg (6800 lbs)

**Documents:**

[Drawing \(PDF\)](#)

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family	Cable Grips
Series	<a href="#">130095</a>
Eye Type	Rotating
O-Ring	N/A
Overview	<a href="#">Pulling Grips</a>
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835851

**Physical**

Approximate Break Strength	3084.43kg (6800 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	15.88-19.05mm (.625-.750")
Color - Grommet	N/A
Eye Diameter	7/8"
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.279m (11.00")
Number of Holes	N/A
Thread Size	N/A

**Material Info**

Engineering Number 35851

**Reference - Drawing Numbers**

Sales Drawing SD-130095-106



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[130095 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300950123](#)