

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950134](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Short Mesh Length 0.838m (33.00"), Approximate Break Strength 21772.43kg (48000 lbs)

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Eye Type Rotating
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Name Heavy Duty
 Type Pulling Grip
 UPC 78678835875

Physical

Approximate Break Strength 21772.43kg (48000 lbs)
 Bale Length N/A
 Body Style Straight
 Cable Diameter 101.60-114.05mm (4.000-4.490")
 Color - Grommet N/A
 Eye Diameter 1 7/8"
 Gender N/A
 Material - Body N/A
 Material - Grip Galvanized Steel
 Mesh Length 0.838m (33.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35875

Reference - Drawing Numbers

Sales Drawing SD-130095-106



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130095 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300950134](#)