

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950136](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.838m (33.00"), Approximate Break Strength 7438.92kg (16400 lbs)

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Eye Type Rotating
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Name Heavy Duty
 Type Pulling Grip
 UPC 78678835881

Physical

Approximate Break Strength 7438.92kg (16400 lbs)
 Bale Length N/A
 Body Style Straight
 Cable Diameter 25.40-37.85mm (1.000-1.490")
 Color - Grommet N/A
 Eye Diameter 1 3/8"
 Gender N/A
 Material - Body N/A
 Material - Grip Galvanized Steel
 Mesh Length 0.838m (33.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 35881

Reference - Drawing Numbers

Sales Drawing SD-130095-107



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130095 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300950136](#)