

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300950142](#)  
**Status:** **Active**  
**Overview:** [Pulling Grips](#)  
**Description:** Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 1.067m (42.00"), Approximate Break Strength 21772.43kg (48000 lbs)

**Documents:**

[Drawing \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159

**General**

Product Family Cable Grips  
 Series [130095](#)  
 Eye Type Rotating  
 O-Ring N/A  
 Overview [Pulling Grips](#)  
 Product Name Heavy Duty  
 Type Pulling Grip  
 UPC 78678835887

**Physical**

Approximate Break Strength 21772.43kg (48000 lbs)  
 Bale Length N/A  
 Body Style Straight  
 Cable Diameter 101.60-114.05mm (4.000-4.490")  
 Color - Grommet N/A  
 Eye Diameter 1 7/8"  
 Gender N/A  
 Material - Body N/A  
 Material - Grip Galvanized Steel  
 Mesh Length 1.067m (42.00")  
 Number of Holes N/A  
 Thread Size N/A

**Material Info**

Engineering Number 35887

**Reference - Drawing Numbers**

Sales Drawing SD-130095-107



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130095 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300950142](#)