

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950249](#)

Status: **Active**

Overview:

Description: Medium Duty Wire Mesh Slack Grip Cable, Split Lace, Double Weave, Offset Eye, Long Mesh Length 0.533m (21.00"), Approximate Break Strength 1360.78kg (3000 lbs)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
Series [130095](#)
Eye Type Offset
O-Ring N/A
Overview support_grips
Product Name Medium Duty
Type Pulling Grip
UPC 78678836130

Physical

Approximate Break Strength 1360.78kg (3000 lbs)
Bale Length N/A
Body Style Straight
Cable Diameter 19.05-25.15mm (.750-.990")
Color - Grommet N/A
Gender N/A
Material - Body N/A
Material - Grip Galvanized Steel
Mesh Length 0.533m (21.00")
Number of Holes N/A
Thread Size N/A

Material Info

Engineering Number 36130

Reference - Drawing Numbers

Sales Drawing SD-130095-117

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[130095](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300950249](#)