

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300950297](#)
Status: **Active**
Overview: [Pulling Grips](#)
Description: Pulling Grips for Fiber Optics, Closed Mesh, Rotating Eye, Bale Length 5", Cable Diameter 5.33-8.89mm (.210-.350"), Approximate Break Strength 680.39kg (1500 lbs)

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130095](#)
 Eye Type Rotating
 O-Ring N/A
 Overview [Pulling Grips](#)
 Product Name Fiber Optic
 Type Pulling Grip
 UPC 78678836661

Physical

Approximate Break Strength 680.39kg (1500 lbs)
 Bale Length 0.120m (4.75")
 Body Style Straight
 Cable Diameter 5.33-8.89mm (.210-.350")
 Color - Grommet N/A
 Gender N/A
 Material - Body Aluminum
 Material - Grip Galvanized Steel
 Mesh Length 0.356m (14.00")
 Number of Holes N/A
 Thread Size N/A

Material Info

Engineering Number 36661

Reference - Drawing Numbers

Sales Drawing SD-130095-118



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130095 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300950297](#)