

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300960078](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: Liquid-Tight Grip Strain Relief for Non-Metallic Type A Flexible Conduit, 1-1/4" NPT, 90° Angle Male, Mesh Length 0.546m (21.50")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Grips
Series	130096
Eye Type	N/A
NEMA Rating	NEMA 4
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Name	Liquid-Tight
Type	Strain Relief Grip
UPC	78678837111
Use With	1 1/4" NPT Lock-Nut 1300990146

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	N/A
Color - Grommet	N/A
Gender	Male
Material - Body	Malleable Iron, Zinc Plated Steel
Material - Grip	Stainless Steel
Mesh Length	0.546m (21.50")
Number of Holes	N/A
Thread Size	1 1/4" NPT

Material Info

Engineering Number	37105-90
--------------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-130096-105
---------------	---------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130096 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300960078](#)