

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990125](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Cord Sealing Grip F4 1" Body Size, 90 Degree, Cable Diameter 17.45-20.62mm (.687-.812"), Stainless Steel Mesh

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family Cable Grips
 Series [130099](#)
 Eye Type N/A
 NEMA Rating NEMA 3R
 O-Ring No
 Overview Strain-Relief Cord Grips
 Product Name MAX-LOC
 Type Strain Relief Grip
 UPC 78678855554
 Use With MAX-LOC Lock Nut 1" NPT [1300990145](#) , MAX-LOC Gasket Sealing Ring 1" NPT [1300990151](#) , MAX-LOC O-Ring, 1" NPT [1301800334](#)

Physical


Approximate Break Strength N/A
 Bale Length N/A
 Body Style 90° Angle
 Cable Diameter 17.45-20.62mm (.687-.812")
 Color - Grommet N/A
 Gender Male
 Material - Body Nylon
 Material - Grip Stainless Steel
 Mesh Length N/A
 Number of Holes 1
 Thread Size 1" NPT

Material Info

Engineering Number 5555M

Reference - Drawing Numbers

Sales Drawing SD-130099-004



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130099](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300990125](#)