

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990158](#)
Status: **Active**
Overview: Strain-Relief Cord Grips
Description: MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 6.35-9.53mm (.250-.375"), Non-Metallic Mesh

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159
 UL E76954

General

Product Family Cable Grips
 Series [130099](#)
 Eye Type N/A
 NEMA Rating NEMA 3R
 O-Ring No
 Overview Strain-Relief Cord Grips
 Product Name MAX-LOC
 Type Strain Relief Grip
 UPC 78678856225
 Use With 3/4" NPT MAX-LOC Lock Nut [1300990144](#) , 3/4" NPT MAX-LOC Gasket Sealing Ring [1300990150](#) , 3/4" NPT MAX-LOC O-Ring [1301800333](#)

Physical

Approximate Break Strength N/A
 Bale Length N/A
 Body Style Straight
 Cable Diameter 6.35-9.53mm (.250-.375")
 Color - Grommet Gray
 Gender Male
 Material - Body Nylon
 Material - Grip Nylon
 Mesh Length N/A
 Number of Holes 1
 Thread Size 3/4" NPT

Material Info

Engineering Number 5622NM

Reference - Drawing Numbers

Sales Drawing SD-130099-005



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130099 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300990158](#)