

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301110024](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Pro-Yellow Stringlight, 150W, 12/2 TC2 with 2.43m Lead, 10 Sockets with Guards, Lamp-It-In-the-Box Packaging, Overall Length 30.48m (100.0'), cULus Listed

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
 Series [130111](#)
 NEMA Configuration NEMA 1-15
 NEMA Rating Rain Tight
 Outlet None
 Overview [Stringlights](#)
 Product Name Pro-Yellow
 Type String Lights
 UPC 78678861202

Physical

Cord Length - Primary 2.43m (8.0')
 Cord Length - Secondary 0.61m (2.0')
 Depth N/A
 Duty General
 Guard Included Yes
 Guard Type Polypropylene
 Height N/A
 Length 30.48m (100.0')
 Material - Guard Polypropylene
 Mounting Style Stringer
 Net Weight 1.360/kg
 Packaging Type Carton
 Socket Construction Assembled

Electrical

Bulb Type Incandescent
 Cord Type - Primary 12/2 TC
 Lamp Type A21
 Lamp Wattage - Maximum 150W
 Lumens 1500
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 302SRL



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130111 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301110024](#) [302SRL](#)