

6

5

4

3

2

1

E

E

D

D

C

C

B

B

A

A

MAX-LOC GRIP  
.56-.68 RANGE  
(5635M)

SINGLE SPEED  
MOMENTARY SWITCH  
(4020)

2-SPEED  
MOMENTARY SWITCH  
(4020-2)

SINGLE SPEED  
MOMENTARY SWITCH  
(4020)

2.6  
66.

10.7  
271.

3.0  
76

NOTE:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

CUSTOMER DRAWING EC NO: WNA2009-0028 DRWN: HKNEELAN 2008/07/11 CHKD: JP 2008/07/11 APPR: JPAWLICK 2008/07/17	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH/MM		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
	▽=0	mm	INCH	DRAWN BY	DATE	TITLE			
	∇=0	4 PLACES	±----	±----	HK	2008/07/11	4026 W/4020-2 IN POSITIONS 3 & 4 AND MESH GRIP 5635M		
		3 PLACES	±----	±----	CHECKED BY	DATE			
		2 PLACES	±----	±----	HK	2008/07/11	MOLEX INCORPORATED		
	1 PLACE	±----	±----	APPROVED BY	DATE				
	ANGULAR ±.5°	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		JP	2008/07/11	MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
A	REV			SIZE A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301260291](#)