

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301280136](#)
Status: **Active**
Description: Heavy Duty Stranded Cable, Type SOOW, 14 AWG, 3 Conductors, 76.20m Length, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	130128
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
UPC	78678879957

Physical

Cable Length	76.20m
Circuits (Loaded)	3
Color - Cable Jacket	Yellow
Insulation	EP Rubber
Net Weight	0.080/kg
Outer Jacket Diameter	13.21mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	14
Wire/Cable Type	SOOW

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Material Info

Engineering Number	SY14-3
--------------------	--------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130128 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130128-0136](#)