

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301350220](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway GFCI Multiple Outlet Box with Ground Continuity Monitor, Open Neutral Relay, (2) NEMA 5-20 Duplex with Flip Lids, 1.83m (6.0') Cord Length, 12/3 SOOW Cord, NEMA 5-20 Plug

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Power Distribution
Series	130135
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Outlet Boxes
Product Name	Super-Safeway
Receptacle Type	Duplex
Type	GFCI Multiple Outlet Box
UPC	78678876133

Physical


Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	1.83m (6.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	2
Packaging Type	Carton

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	Yes
Ground Continuity Monitor	Yes
NEMA Configuration	NEMA 5-20
Voltage - Maximum	120V

Material Info

Engineering Number	32GM20L123
--------------------	------------



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130135 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301350220](#)