

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301350315](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Watertite GFCI Multiple Outlet Box with Open Neutral Relay, (6)NEMA 5-20 Outlets with Flip Lids, 1.83m (6.0') Cord Length, NEMA 5-20 Plug

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Power Distribution
 Series [130135](#)
 Enclosure Rating NEMA 4X
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Outlet Boxes](#)
 Product Name Watertite
 Receptacle Type Duplex
 Type GFCI Multiple Outlet Box
 UPC 78678861594

Physical

Cord Diameter 15.24mm (.600")
 Cord Grip Body Size F2 1/2"
 Cord Length 1.83m (6.0')
 Feed-Thru No
 Flip Lid Yes
 Material - Housing Nylon
 Net Weight 2.934/kg
 Number of Receptacles 3
 Packaging Type Carton

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 20.0A
 GFCI Yes
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-20
 Voltage - Maximum N/A

Material Info

Engineering Number 3494



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130135 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301350315](#)