

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370158](#)
Status: **Active**
Overview: Watertite Extreme Wet-Location Wiring Solutions
Description: Super-Safeway Multiple Outlet Box, Extended Depth, (1) NEMA 5-15 GFCI Receptacles with Flip Lid, Open Neutral Relay, 7.62m (25.0') Cord Length, 14/3 SOOW Cord, 5-15 Plug

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	Yes
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Super-Safeway
Receptacle Type	GFCI Duplex
Type	Multiple Outlet Box
UPC	78678800790

Physical

Cord Diameter	13.59mm (.535")
Cord Grip Body Size	F3 3/4"
Cord Length	7.62m (25.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Number of Receptacles	1
Packaging Type	Carton

Electrical

Cord Type	14/3 SOOW
Current - Maximum per Contact	15.0A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	NEMA 5-15
Voltage - Maximum	120V

Material Info

Engineering Number 3070-GFIA143



EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130137 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301370158](#)