

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430226](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** [Watertite Extreme Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 30.48m \(100.0'\), NEMA L5-20 125V](#)

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family [Wiring Devices](#)  
 Series [130143](#)  
 IP Rating IP67  
 NEMA Configuration NEMA L5-20  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Watertite Extreme  
 Receptacle Type Single  
 Specialty N/A  
 Type Cordset  
 UPC 78678871240

**Physical**

Cord Grip Body Size F3 3/4"  
 Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 30.48m (100.0')  
 Locking Blade Yes  
 Net Weight 159.000/kg  
 Poles 2-pole/3-wire

**Electrical**

Cord Type 12/3 SOOW  
 Current - Maximum per Contact 20.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V

**Material Info**

Engineering Number 26W47D123



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301430226](#)