

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430248](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Watertite Cordset 14 Gauge SOOW, 4 Pole/5 Wire, Cordset Length 7.62m (25.0'), NEMA L21-20, 208V

**Agency Certification**

CSA	LR6837
UL	E38085

**General**

Product Family	Wiring Devices
Series	<a href="#">130143</a>
IP Rating	IP67
NEMA Configuration	NEMA L21-20
Overview	wet_location__watertite174
Product Name	Watertite
Receptacle Type	Single
Specialty	N/A
Type	Cordset
UPC	78678863042

**Physical**

Cord Grip Body Size	F3 3/4"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	Yes
Net Weight	288.000/kg
Poles	4-pole/5-wire

**Electrical**

Cord Type	12/3 SOOW
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3Ø 208V

**Material Info**

Engineering Number	26W81A145
--------------------	-----------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301430248](#)