

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470111](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Connector with Locking Blade, 3 Pole/4 Wire, NEMA L17-30, 3ø 600V, Cord Grip Body Size F4

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130147](#)
 IP Rating IP67
 NEMA Configuration NEMA L17-30
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type Single
 Specialty N/A
 Type Connector
 UPC 78678871336

Physical

Cord Grip Body Size F4 1"
 Flange No
 Flip Lid No
 Gender Female
 Length N/A
 Locking Blade Yes
 Poles 3-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 3ø 600V

Material Info

Engineering Number 29W77

Reference - Drawing Numbers

Sales Drawing 1301470111-000



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301470111](#) [29W77](#)