

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470139](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 4 Pole/4 Wire, Non-NEMA, 208V

Documents:

| | |
|--------------------------------|--|
| 3D Model | Brochure (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Drawing (PDF) | |

Agency Certification

UL E68122

General

| | |
|--------------------|---|
| Product Family | Wiring Devices |
| Series | 130147 |
| IP Rating | IP67 |
| NEMA Configuration | Non-NEMA Locking |
| Overview | Watertite Extreme Wet-Location Wiring Solutions |
| Product Name | Watertite Extreme |
| Receptacle Type | Single |
| Specialty | N/A |
| Type | Receptacle |
| UPC | 78678871591 |

Physical

| | |
|---------------|---------------|
| Flange | No |
| Flip Lid | Yes |
| Gender | Female |
| Length | N/A |
| Locking Blade | Yes |
| Poles | 4-pole/4-wire |

Electrical

| | |
|-------------------------------|-------|
| Cord Type | N/A |
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Lighted Connector | No |
| Voltage - Maximum | 208V |

Material Info

Engineering Number 67W09

Reference - Drawing Numbers

Sales Drawing 1301470139-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301470139](#) [67W09](#)