

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301490027](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Safeway Flanged Inlet with Locking Blade, 2 Pole/3 Wire, NEMA L5-20, 125V

Documents:

| | |
|--------------------------------|--|
| 3D Model | Brochure (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Drawing (PDF) | |

Agency Certification

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E10176 |

General

| | |
|--------------------|--|
| Product Family | Wiring Devices |
| Series | 130149 |
| IP Rating | N/A |
| NEMA Configuration | NEMA L5-20 |
| Overview | Heavy-Duty Industrial Wiring Devices |
| Product Name | Safeway |
| Receptacle Type | Single |
| Specialty | N/A |
| Type | Inlet |
| UPC | 78678802647 |

Physical

| | |
|---------------|---------------|
| Flange | Yes |
| Flip Lid | No |
| Gender | Male |
| Length | N/A |
| Locking Blade | Yes |
| Poles | 2-pole/3-wire |

Electrical

| | |
|-------------------------------|-------|
| Cord Type | N/A |
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Lighted Connector | No |
| Voltage - Maximum | 125V |

Material Info

| | |
|--------------------|--------|
| Engineering Number | 2647MB |
|--------------------|--------|

Reference - Drawing Numbers

| | |
|---------------|----------------|
| Sales Drawing | 1301490027-000 |
|---------------|----------------|



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[130149 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301490027](#)