

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301490047](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Flanged Inlet with Locking Blade, 4 Pole/4 Wire, Non-NEMA, 208V

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E10176

**General**

Product Family [Wiring Devices](#)  
 Series [130149](#)  
 IP Rating N/A  
 NEMA Configuration Non-NEMA Locking  
 Overview [Heavy-Duty Industrial Wiring Devices](#)  
 Product Name Safeway  
 Receptacle Type N/A  
 Specialty N/A  
 Type Inlet  
 UPC 78678802809

**Physical**

Flange Yes  
 Flip Lid No  
 Gender Male  
 Length N/A  
 Locking Blade Yes  
 Poles 4-pole/4-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 208V

**Material Info**

Engineering Number 2809MB



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130149 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301490047](#)