

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530051](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA 5-15, 15A, 120V, 1.83m (6.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 4
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Name Safeway
 Receptacle Type N/A
 Type GFCI Commercial Duty, Single Phase
 UPC 78678828406

Physical

Cord Diameter 9.40mm (.370")
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length 1.83m (6.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Number of Receptacles 1
 Packaging Type Bag

Electrical

Cord Type 14/3 SJTW
 Current - Maximum per Contact 15.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 120V AC

Material Info

Engineering Number 15051-6



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130153 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301530051](#)