

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530137](#)
Status: **Active**
Overview: Ground Fault Circuit Interrupter (GFCI) Products
Description: Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Outlet Box, NEMA 5-20 Double Duplex, 15A, 120V, 0.61m (2.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 4
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Name Safeway
 Receptacle Type Duplex
 Type GFCI Commercial Duty, Single Phase
 UPC 78678828423

Physical

Cord Diameter 10.92mm (.430")
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length 0.61m (2.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Number of Receptacles 2
 Packaging Type Bag

Electrical

Cord Type 12/3 SJTW
 Current - Maximum per Contact 20.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-20
 Voltage - Maximum 240V

Material Info

Engineering Number 20053-2



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130153 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301530137](#)