

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302090056](#)
Status: **Active**
Description: Micro-Change Stranded Cable, Shielded PVC, 22 AWG, 3 Conductors, 76.20m Length, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	130209
Crimp Quality Equipment	Yes
Product Name	Micro-Change (M12)
UPC	78678833491

Physical

Cable Length	76.20m
Circuits (Loaded)	3
Color - Cable Jacket	Yellow
Material - Outer Jacket	PVC
Net Weight	15.422/g
Outer Jacket Diameter	5.72mm
Packaging Type	Carton
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	22
Wire/Cable Type	Shielded PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V

Material Info

Engineering Number	85-2231M
--------------------	----------

Image coming soon

Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[130209 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1302090056](#)