

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302100025](#)
Status: **Active**
Description: Micro-Change Stranded Cable, PVC, 24 AWG, 4 Conductors, 76.20m Length, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	130210
Crimp Quality Equipment	Yes
Product Name	Micro-Change (M12)
UPC	78678825909

Physical

Cable Length	76.20m
Circuits (Loaded)	4
Color - Cable Jacket	Yellow
Material - Outer Jacket	PVC
Net Weight	8.618/g
Outer Jacket Diameter	4.57mm
Packaging Type	Carton
Temperature Range - Operating	-20° to +105°C
Wire Size AWG	24
Wire/Cable Type	PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V

Material Info

Engineering Number	84-2440
--------------------	---------



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[130210 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1302100025](#)