

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1302261845](#)  
**Status:** **Active**  
**Description:** Heavy Duty Stranded Cable, Rubber, 12 AWG, 12 Conductors, 304.80mm Length, Black

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">130226</a>
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
UPC	78678882959

**Physical**

Cable Length	304.80mm (1.0')
Circuits (Loaded)	12
Color - Cable Jacket	Black
Net Weight	498.950/g
Outer Jacket Diameter	26.54mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +90°C
Wire Size AWG	12
Wire/Cable Type	Rubber

**Electrical**

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	R62161212
--------------------	-----------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130226](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1302261845](#)