


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1510132506](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid Connector System](#)  
**Description:** 2.00mm Pitch, Milli-Grid BMI PCB Header, Dual Row, Vertical, Through Hole, 6 Circuits, 0.76µm Gold (Au) Plating, 2.10mm Tail Length, Tube, Lead-Free

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Application Specification 503940002-AS-000 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-151013-0001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-151013-0001-001 (PDF)</a>	



**General**

Product Family	PCB Headers
Series	<a href="#">151013</a>
Application	Panel-to-Board, Signal, Wire-to-Board
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid BMI
UPC	889056565318

**Physical**

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.830/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	2.10mm
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[151013 Series](#)

**Mates With**

Milli-Grid Wire-to-Board Receptacle Housing [51110](#) , Milli-Grid Panel-to-Board Receptacle Housing [151014](#)

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	005
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

**Material Info****Reference - Drawing Numbers**

Application Specification	503940002-AS-000
Packaging Specification	PK-151013-0001-001
Product Specification	PS-151013-0001-001
Sales Drawing	SD-151013-0001-000

This document was generated on 09/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151013-2506](#)