

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1511181370](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid Connector System](#)  
**Description:** 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Vertical, Surface Mount, 0.75µm Gold (Au) Plating, with Peg, without Pick and Place Cap, 20 Circuits, Glow-Wire Capable, Tube

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 503940002-AS-000 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-151118-0001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-151118-3000-001 (PDF)</a>
<a href="#">Product Specification PS-151117-0001-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 503940001-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">151118</a>
Application	Board-to-Board, Signal, Wire-to-Board
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid
UPC	889056796651

**Physical**

Breakaway	No
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.904/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.750µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[151118 Series](#)

**Mates With**

Milli-Grid Receptacle Housing [151192](#) ,  
[51110](#) <br> Milli-Grid PCB Receptacles  
[78787](#) , [78788](#) , [79107](#) , [79109](#)

Termination Interface: Style Surface Mount

**Electrical**

Current - Maximum per Contact 2.0A  
Voltage - Maximum 125V AC

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 010  
Lead-free Process Capability REFLOW  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Application Specification 503940001-AS-000, 503940002-AS-000  
Packaging Specification PK-151118-0001-001, PK-151118-3000-001  
Product Specification PS-151117-0001-001  
Sales Drawing SD-151118-0001-001

This document was generated on 09/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151118-1370](#)