

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552200138](#)  
**Status:** **Active**  
**Overview:** Flamar Standard and Custom Cables for Industrial Automation  
**Description:** Flamar Control Cable, WSOR Jacket, Unshielded, 2 Circuits, 0.75mm<sup>2</sup> / 19 AWG, 6.00mm (.236") Diameter, 1000.0m (3280.83') Length, Gray

**Documents:**

[Product Specification 1552200001-P1E \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155220</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Signal and Control
UPC	889056459426

**Physical**

Bending Radius - Minimum	> 7.5xOD
Cable Length	1000.0m
Circuits (Loaded)	2
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	6.00mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	19
Wire Size mm <sup>2</sup>	0.75
Wire/Cable Type	UL AWM 21215 / CSA

**Electrical**


Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

**Material Info**

Engineering Number	1X1000M
--------------------	---------

**Reference - Drawing Numbers**

Product Specification	1552200001-P1E
-----------------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155220](#) Series

**Use With**

DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#) <br>Micro-Change (M12) [120071](#) <br>Ultra-Lock (M12) [120085](#) <br>GWconnect Heavy Duty Connectors [93601](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-0138](#)