

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552200169](#)  
**Status:** **Active**  
**Overview:** Flamar Standard and Custom Cables for Industrial Automation  
**Description:** Flamar Control Cable, WSOR Jacket, Unshielded, 4 Circuits, 1.00mm<sup>2</sup> with Green-Yellow Ground / 18 AWG with Green-Yellow Ground, 7.60mm (.299") Diameter, 300.0m (984.25') Length, Black

**Documents:**

[Product Specification 1552200001-P1E \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

UL      E172949

**General**

Product Family      Cable  
Series      [155220](#)  
Comments      3 reels of 100.0m each  
Crimp Quality Equipment      Yes  
Geographic Area      Global  
Overview      [Flamar Standard and Custom Cables for Industrial Automation](#)  
Product Name      Flamar, Signal and Control  
UPC      889056460033

**Physical**

Bending Radius - Minimum      > 7.5xOD  
Cable Length      300.0m  
Circuits (Loaded)      4  
Color - Cable Jacket      Black  
Insulation      TPE  
Material - Outer Jacket      WSOR  
Net Weight      0.083/kg  
Outer Jacket Diameter      7.60mm  
Packaging Type      Reel  
Temperature Range - Operating      -25° to +80°C  
Wire Size AWG      18  
Wire Size mm<sup>2</sup>      1.00  
Wire/Cable Type      UL AWM 21215 / CSA

**Electrical**


Current - Maximum per Contact      Contact Molex  
Voltage - Maximum      600V

**Material Info**

Engineering Number      3X100M

**Reference - Drawing Numbers**

Product Specification      1552200001-P1E



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[155220](#) Series

**Use With**

DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#)  
<br>Micro-Change (M12) [120071](#) <br>Ultra-Lock (M12) [120085](#) <br>GWconnect Heavy Duty Connectors [93601](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-0169](#)