


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1553312008](#)

**Status:** **Active**

**Overview:** Flamar Standard and Custom Cables for Industrial Automation

**Description:** Flamar Power Cable, PUR Jacket, Braided Shielding Overall, 8 Circuits, 4x(4.00mm<sup>2</sup>) with Green-Yellow Ground + 2x(2x1.50mm<sup>2</sup> with Braided Shield) / 4x(12 AWG) with Green-Yellow Ground + 2x(2x16 AWG with Braided Shield), 15.80mm (.228") Diameter, 250.0m (820.21') Length, Orange



**Documents:**

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155331</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Servo Motor
UPC	889056461924

**Physical**

Bending Radius - Minimum	> 10xOD
Cable Length	250.0m
Circuits (Loaded)	8 (4+2+2)
Color - Cable Jacket	Orange
Insulation	TPE
Material - Outer Jacket	PUR
Net Weight	0.010/g
Outer Jacket Diameter	15.80mm
Packaging Type	Reel
Temperature Range - Operating	-40° to +80°C
Wire Size AWG	12, 16
Wire Size mm <sup>2</sup>	1.50, 4.00
Wire/Cable Type	UL AWM 21223 / CSA

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V

**Material Info**

Engineering Number	1X250M
--------------------	--------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155331](#) Series

**Use With**

Brad M23 [120230](#) , [120233](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155331-2008](#)