

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1731120228](#)  
**Status:** **Active**  
**Overview:** [FCT D-Sub Connectors](#)  
**Description:** FCT Machined Contact, Female, Crimp, 1.30µm Gold Plating, Split Tine, 22-28 AWG

**Documents:**

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**General**

Product Family	D-Sub Products
Series	<a href="#">173112</a>
Contact Type	Machined Crimp
Overview	<a href="#">FCT D-Sub Connectors</a>
Product Category	Contacts
Product Name	FCT Products
Type	High Density
UPC	889056489836

**Physical**

Durability (mating cycles max)	500
Gender	Female
Material - Contact	Brass
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	1.300µm
Plating min - Termination	1.300µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size AWG	22, 24, 26, 28

**Electrical**

Current - Maximum per Contact	5.0A
-------------------------------	------

**Material Info**

Engineering Number	FK22SL-13V-5783
--------------------	-----------------

**Reference - Drawing Numbers**

Sales Drawing	1731120223-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - ED/71/2019 (16 July 2019)

Lead

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[173112 Series](#)

**Use With**

FCT High-Density Connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173112-0228](#)