

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2018450030](#)  
**Status:** **Active**  
**Overview:** MultiCat Power Connectors with Precision-Machined Contacts  
**Description:** MultiCat High-Power Plug Terminal, Gold over Nickel Phosphorus Plating, 10-12 AWG

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification 2018460001-PK (PDF)</a>
<a href="#">Product Specification 2009140003-000 (PDF)</a>	<a href="#">Test Summary 2009140003-TS-000 (PDF)</a>
<a href="#">Product Specification 2018400000-PS-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification 2009140003-AS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2018400000-AS-000 (PDF)</a>	



*Series image - Reference only*

**General**

Product Family	Crimp Terminals
Series	<a href="#">201845</a>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">MultiCat Power Connectors with Precision-Machined Contacts</a>
Product Name	MultiCat
UPC	889056747318

**Physical**

Durability (mating cycles max)	500
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Net Weight	2.228/g
Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.40mm-4.03mm
Wire Size AWG	10, 12
Wire Size mm <sup>2</sup>	3.31-5.26

**Electrical**

Current - Maximum per Contact	30.0A
Voltage - Maximum	1000V AC

**Material Info**

Engineering Number	FPG008P204
--------------------	------------

**Reference - Drawing Numbers**

Application Specification	2009140003-AS-000, 2018400000-AS-000
Packaging Specification	2018460001-PK
Product Specification	2009140003-000, 2018400000-PS-000
Sales Drawing	2018450030-000
Test Summary	2009140003-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[201845](#) Series

**Use With**

MultiCat High-Power Circular Plug Housing [200914](#) . MultiCat High-Power Inline Plug Housing [201840](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Crimp Tool for MultiCat Machined High-Power Contact, 8-18 AWG	<a href="#">2002182300</a>
Extraction Tool for MultiCat High-Power	<a href="#">2002220200</a>

This document was generated on 09/22/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201845-0030](#)