

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2046010001](#)
Status: **Active**
Overview: Coeur CST High-Current Interconnect System
Description: Coeur CST High-Current 8.00mm Receptacle Crimp Housing, Single Row, 2 Circuits

Documents:

3D Model	Application Specification 2043130001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 2046010001-PK-000 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2043130001-PS-000 (PDF)	

General

Product Family	Crimp Housings
Series	204601
Application	Power, Wire-to-Board
Diameter	8.00mm
Overview	Coeur CST High-Current Interconnect System
Product Name	Coeur CST
UPC	191128427456

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	22.600/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	N/A
Pitch - Mating Interface	25.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	2043130001-AS-000
Packaging Specification	2046010001-PK-000
Product Specification	2043130001-PS-000
Sales Drawing	2045990001-SD-000



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[204601](#) Series

Mates With

8.00mm Male Header [204600](#)

Use With

8.00mm Female Crimp Socket [204608](#)

8.00mm Terminal Retention Housing [204603](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[204601-0001](#)