

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200860348](#)  
**Status:** **Active**  
**Overview:** [Brad Nano-Change \(M8\) Products](#)  
**Description:** Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 24 AWG, PUR Cable, 5.0m (16.40') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120086](#)  
 Connector End A Nano-Change (M8)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Nano-Change \(M8\) Products](#)  
 Product Name Nano-Change (M8)  
 Region America  
 Type Single Ended  
 UPC 78678832945

**Physical**

Cable Diameter 4.57mm (.180")  
 Cable Length 5.0m (16.40')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Female-Pigtail  
 Keyway A-coded  
 LED Indicator No  
 Material - Cable Jacket PUR  
 Material - Connector Body TPE  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Orientation 90° to Pigtail  
 Poles 3  
 Temperature Range - Operating -25° to +80°C  
 Wire Size AWG 24  
 Wire/Cable Type E152210

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 60V AC / 75V DC

**Material Info**

Engineering Number 403001B09M050

**Reference - Drawing Numbers**

Sales Drawing SD-120086-019-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120086 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200860348](#) [403001B09M050](#)