

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200948013](#)
Status: **Active**
Overview: Brad M23 Signal and Power Connectors
Description: Brad M23 Single-Ended Cordset, 12 Poles, Female (90°) to Pigtail, 18/22 AWG, PUR Cable, 10.0m (32.81') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120094
Connector End A	M23
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	883906359201

Physical

Cable Diameter	N/A
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Pigtail
Poles	12
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	18, 22
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	6.0A
Voltage - Maximum	63V AC/DC

Material Info

Engineering Number	K02201P80M100
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-120094-012
---------------	---------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120094](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200948013](#)