

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300610119](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower A-Size (7/8"-M22) Single-Ended Cordset, 4 Poles, Female (90°) to Straight, 14 AWG, Gray PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Cordsets
 Series [130061](#)
 Connector End A BradPower A-Size (7/8"-M22)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower A-Size
 Protocol FF
 Region Europe
 Type Single Ended
 UPC 78678883192

Physical

Cable Diameter 14.99mm (.590")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Gray
 Coupling Style Threaded
 Gender Female-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPE
 Material - Coupling Nut Black Epoxy Coated Zinc
 Material - Plating Mating Gold
 Net Weight 254.000/g
 Orientation 90° to Pigtail
 Poles 4
 Temperature Range - Operating -20° to +90°C
 Wire Size AWG 14
 Wire/Cable Type ST00W

Electrical


Current - Maximum per Contact 15.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 104001A46M020

Reference - Drawing Numbers

Sales Drawing SD-130061-014-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

Search Parts in this Series

[130061](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300610119](#) [104001A46M020](#)