

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301540048](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Standard Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LL52750
 UL E38085

General

Product Family Wiring Devices
 Series [130154](#)
 IP Rating IP67
 NEMA Configuration NEMA 5-15
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type Duplex
 Specialty N/A
 Type Molded Y Cordset
 UPC 78678801400

Physical

Cord Grip Body Size F2 1/2"
 Flange No
 Flip Lid No
 Gender Male-Female
 Length 0.91m (3.0')
 Locking Blade No
 Net Weight 1023.757/g
 Poles 2-pole/3-wire

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 15.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V

Material Info

Engineering Number 14W47-Y

Reference - Drawing Numbers

Sales Drawing 1301540048-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130154 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301540048](#) [14W47-Y](#)