

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0153660254**
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 76.00mm Cable Length, Tin (Sn) Plating, 24 Circuits, with Shield

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification 153660001-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15366
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	193264622788

Physical

Cable Length	76.00mm
Circuits (Loaded)	24
Contact Layout Type	D (opposite side)
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	N/A

Material Info

Reference - Drawing Numbers

Product Specification	153660001-000
Sales Drawing	153660001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

15366 Series

Mates With

Easy-On FFC/FPC Connector [524352433](#)
, [524372433](#) , [5019512400](#) , [525592433](#) ,
[525592434](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15366-0254](#)