

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011273](#)

Status: **Active**

Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)

Description: GWconnect STD-HV - Standard-High Voltage, Double Lever Surface Mount Housing, Die-cast Aluminum, with 4 Pegs, with Cover, with Gasket, Size 10B «57x27», Pg16 Thread, Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Double Lever SMT Housing
IP Rating	IP66, IP69 coupled and blocked lever
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191881300

Physical

Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Peg	Stainless Steel
Mounting Style	Surface Mount
Number of Pegs	4
Packaging Type	Bag
Thread Size	Pg16
Thread Type	(Pg)

Electrical

Voltage - Maximum	830V
-------------------	------

Material Info

Engineering Number	7810.5025.2
--------------------	-------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 10B «57x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1273](#)