

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200845109](#)
Status: **Active**
Overview:
Description: Ultra-Lock (M12) Receptacle, 5 Poles, PG9 Mounting Threads, Male (Straight) to 0.34mm² PVC Leads, 0.30m (11.81") Length

General

Product Family	Industrial Receptacles
Series	120084
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	ultralock_connection_system
Product Name	Ultra-Lock (M12)
Type	Single Ended (pigtail)
UPC	883906778927

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	23.586/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	22
Wire/Cable Type	UL 1569

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Material Info

Engineering Number	WR5J26E03C3003
--------------------	----------------

Reference - Drawing Numbers

Sales Drawing	SD-120084-026-001
---------------	-------------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120084](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200845109](#)