

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301530110](#)
Status: **Active**
Overview: [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
Description: Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E66308

General

Product Family Power Distribution
 Series [130153](#)
 Enclosure Rating NEMA 4X
 GFCI Reset Manual
 Mounting Style Portable
 Open Neutral Relay Yes
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)
 Product Name Super-Safeway
 Receptacle Type N/A
 Type GFCI Industrial Duty, Single Phase
 UPC 78678889742

Physical

Cord Diameter 10.67mm (.420")
 Cord Grip Body Size Internal Double C-Clamp
 Cord Length 0.61m (2.0')
 Feed-Thru Yes
 Flip Lid No
 Material - Housing Nylon
 Net Weight 680.388/g
 Number of Receptacles 0
 Packaging Type Bag

Electrical

Cord Type 12/3 SJEOOW
 Current - Maximum per Contact 20.0A
 GFCI Yes-In-line
 Ground Continuity Monitor No
 NEMA Configuration N/A
 Voltage - Maximum 120V

Material Info

Engineering Number 20051-0M



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130153 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1301530089](#)