

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552400189](#)

**Status:** **Active**

**Overview:** Flamar Standard and Custom Cables for Industrial Automation

**Description:** Flamar Control Cable, TPE Jacket, Unshielded, 5 Circuits, 1.50mm<sup>2</sup> with Green-Yellow Ground / 16 AWG with Green-Yellow Ground, 10.00mm (.394") Diameter, 1000.0m (3280.83') Length, Gray

**Documents:**

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155240</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Signal and Control
UPC	889056456180

**Physical**


Bending Radius - Minimum	> 10xOD
Cable Length	1000.0m
Circuits (Loaded)	5
Color - Cable Jacket	Gray
Insulation	PVC
Material - Outer Jacket	TPE
Net Weight	0.010/g
Outer Jacket Diameter	10.00mm
Packaging Type	Wooden Drum
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	16
Wire Size mm <sup>2</sup>	1.50
Wire/Cable Type	UL Listed PLTC

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V

**Material Info**

Engineering Number	1X1000M
--------------------	---------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155240 Series](#)

**Use With**

DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#) <br>Micro-Change (M12) [120071](#) <br>Ultra-Lock (M12) [120085](#) <br>GWconnect Heavy Duty Connectors [93601](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155240-0189](#)