

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [15-24-4742](#)  
**Status:** **Active**  
**Overview:** Disk Drive Power Connector  
**Description:** 5.08mm Pitch Disk Drive Power Connection System Header, Vertical, Through Hole, 4 Circuits, Lead-Free, 2.12mm PC Tail Length, with PCB Locator Peg

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**Agency Certification**


CSA LR19980  
 UL E29179

**General**

Product Family PCB Headers  
 Series [8981](#)  
 Application Power, Wire-to-Board  
 Overview [Disk Drive Power Connector](#)  
 Product Name Disk Drive Power  
 UPC 822348644513

**Physical**

Breakaway No  
 Circuits (Loaded) 4  
 Circuits (maximum) 4  
 Color - Resin Black  
 Durability (mating cycles max) 25  
 First Mate / Last Break No  
 Flammability 94V-0  
 Glow-Wire Compliant No  
 Guide to Mating Part No  
 Keying to Mating Part None  
 Lock to Mating Part Yes  
 Mated Height 24.00mm  
 Material - Metal Phosphor Bronze  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin High Temperature Thermoplastic  
 Net Weight 1.918/g  
 Number of Rows 1  
 Orientation Vertical  
 PC Tail Length 2.12mm  
 PCB Locator Yes  
 PCB Retention None  
 PCB Thickness - Recommended 1.60mm  
 Packaging Type Tray  
 Pitch - Mating Interface 5.08mm  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Polarized to Mating Part Yes  
 Polarized to PCB Yes  
 Shrouded Fully  
 Stackable No  
 Surface Mount Compatible (SMC) Yes  
 Temperature Range - Operating -40°C to +105°C



*image - Reference only*

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[8981Series](#)

**Mates With**

[15-24-4048 \(89814P\)](#) Disk Drive Power Connection System Female Crimp Housing with Terminal [02-08-1201 \(8980-3C\)](#) or [02-08-1202 \(8980-3L\)](#)

Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 6.5A  
Voltage - Maximum 250V AC

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 10  
Lead-free Process Capability SMC & Wave Capable (TH only)  
Max. Cycles at Max. Process Temperature 1  
Process Temperature max. C 265

**Material Info**

Old Part Number A-8981-4V6-LF

**Reference - Drawing Numbers**

Sales Drawing SD-8981-4V6

This document was generated on 06/18/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-24-4742](#)