

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190700033**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Ring Tongue Terminal for 18-22 AWG Wire

Documents:

| | |
|--|--|
| 3D Model | Product Specification PS-19902-011-001 (PDF) |
| Drawing (PDF) | Product Specification PS-19902-013-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-19902-009-001 (PDF) | |

Agency Certification

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

General

| | |
|-------------------------|-----------------------------|
| Product Family | Ring and Spade Terminals |
| Series | <u>19070</u> |
| Crimp Quality Equipment | Yes |
| Overview | <u>Solderless Terminals</u> |
| Product Name | InsulKrimp |
| Type | Ring |
| UPC | 800753068957 |

Physical

| | |
|------------------------------|----------------------|
| Barrel Type | Closed |
| Flammability | 94V-0 |
| Insulation | PVC |
| Material - Plating Mating | Tin |
| Net Weight | 1.072/g |
| Packaging Type | Bag |
| Stud Size | 3/8" (M9) |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 3.70mm max. |
| Wire Size AWG | 18, 20, 22 |
| Wire Size mm ² | 0.35-0.80 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

| | |
|--------------------|------------|
| Engineering Number | AA-226-38X |
|--------------------|------------|

Reference - Drawing Numbers

| | |
|-----------------------|---|
| Product Specification | PS-19902-009-001, PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing | SD-19070-003-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19070 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

| | |
|--------------|------------------|
| PremiumGrade | <u>640010100</u> |
|--------------|------------------|

Hand Crimp Tool for Avikrimp and InsulKrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)

| | |
|--------------|------------------|
| PremiumGrade | <u>640010300</u> |
|--------------|------------------|

Hand Crimp Tool for InsulKrimp Terminals and Splices, 10-22

AWG (Rings,
Spades, Hooks,
Block Spades and
Flanged Spades)
Crimp Head for the 640050100
AT-200 Pneumatic
Hand Tool
Crimp Head for the 640050300
AT-200 Pneumatic
Hand Tool
ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 10/12/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19070-0033](#)